

### designed for scientists



## **Tube Mill 100 con. Pharma Solution**

/// Data Sheet

Fast grinding of tablets without the risk of cross-contamination:

Many standardized test procedures in the pharmaceutical industry, such as pharmacopoeia tests as described in official compendia (United States Pharmacopeia (USP 905), European Pharmacopoeia (PhEur 2.9.40) etc.), require the grinding and dissolution of tablets as the first step before further analysis. The challenges in sample preparation include the avoidance of cross-contamination between sample batches, time-consuming cleaning and the often small sample quantities.





### designed for scientists

The Tube Mill 100 control Pharma Solution package, consisting of the Tube Mill 100 control batch mill and patented disposable plastic chambers with a volume of 100 ml (MT 100.10), was specially put together by the IKA product experts to address these challenges.

Grinding, storage and transport of the samples takes place in a closed, disposable grinding chamber which eliminates the risk of cross-contamination between different batches. The time-consuming cleaning of the mill and the containers after each cycle is also eliminated. The MT grinding chambers are designed to process even the smallest sample quantities from 1 gram (e. g. a single tablet).

The Tube Mill 100 control is a batch mill for grinding hard, brittle and dry materials up to Mohs hardness 5. With its disposable and reusable grinding chambers with volumes of 40 ml or 100 ml, it is versatile and can be used for a wide range of requirements.





# designed for scientists

#### **Technical Data**

Motor rating input [W]	100
Motor rating output [W]	80
Speed range [rpm]	5000 - 25000
Process type	batch
Circumferential speed max. [m/s]	65
Useable volume max. [ml]	100
Feed hardness max. [Mohs]	5
Feed grain size max. [mm]	10
Power-ON time [min]	3
Mill feed can be cooled in milling chamber with dry ice	yes
Operating principle	cutting/impact
Speed deviation [%]	±2
Dimensions (W x H x D) [mm]	180 x 212 x 300
Weight [kg]	2.8
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 30
USB interface	yes
Voltage [V]	220 - 240
Frequency [Hz]	50/60
Power input [W]	100







